



Dealers Industrial Equipment

No.:

Date: 23-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 326T
Output : 50 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1780 rpm
Slip : 1.11 %
Voltage : 575 V
Rated current : 48.5 A
Locked rotor current : 354 A
Locked rotor current (I_L/I_n) : 7.3
No-load current : 22.0 A
Full load torque : 146 lb.ft
Locked rotor torque : 260 %
Breakdown torque : 280 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 20 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 706 lb
Moment of inertia : 9.1624 sq.ft.lb
Noise level : 71 dB(A)

	D.E.	N.D.E.
Bearings	6312 2RS-C3	6212 2RS-C3
Regreasing interval	---	---
Grease amount	---	---

Load	Power factor	Efficiency (%)
100%	0.81	94.5
75%	0.76	94.5
50%	0.65	93.6

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #05018XT3H326T

Performed by

Checked