



Dealers Industrial Equipment

No.:

Date: 27-SEP-2016

DATA SHEET

Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Oil Well Pumping : High Slip - NEMA Design "D" - ODP

Frame : 405T
Output : 60 HP
Frequency : 60 Hz
Poles : 6
Full load speed : 1125 rpm
Slip : 6.25 %
Voltage : 208-230/460 V
Rated current : 166-150/75.1 A
Locked rotor current : 856/428 A
Locked rotor current (I_L/I_N) : 5.7
No-load current : 58.0/29.0 A
Full load torque : 276 lb.ft
Locked rotor torque : 280 %
Breakdown torque : 0 %
Design : D
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 25 s (hot)
Service factor : 1.00
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP23
Approximate weight : 930 lb
Moment of inertia : 27.923 sq.ft.lb
Noise level : 69 dB(A)

	D.E.	N.D.E.
Bearings	NU-316 C3	6314 C3
Regreasing interval	20000 h	20000 h
Grease amount	34 g	27 g

Load	Power factor	Efficiency (%)
100%	0.85	88.5
75%	0.81	89.0
50%	0.70	88.5

Notes:

Downloaded from <http://dealerselectric.com>
Generated for Model #06012OS3EOW405T

Performed by

Checked