



Dealers Industrial Equipment

No.:

Date: 28-SEP-2016

DATA SHEET Three-phase induction motor - Squirrel cage rotor

Customer :
Product line : Three-Phase : Explosion Proof - NEMA Premium

Frame : 444/5T
Output : 125 HP
Frequency : 60 Hz
Poles : 4
Full load speed : 1785 rpm
Slip : 0.83 %
Voltage : 460 V
Rated current : 142 A
Locked rotor current : 909 A
Locked rotor current (I_L/I_n) : 6.4
No-load current : 46.3 A
Full load torque : 363 lb.ft
Locked rotor torque : 200 %
Breakdown torque : 220 %
Design : B
Insulation class : F
Temperature rise : 80 K
Locked rotor time : 18 s (hot)
Service factor : 1.15
Duty cycle : S1
Ambient temperature : -20°C - +40°C
Altitude : 1000 m
Degree of Protection : IP55
Approximate weight : 2026 lb
Moment of inertia : 57.163 sq.ft.lb
Noise level : 76 dB(A)

| | D.E. | N.D.E. |
|---------------------|---------|---------|
| Bearings | 6219 C3 | 6316 C3 |
| Regreasing interval | 8033 h | 8569 h |
| Grease amount | 27 g | 34 g |

| Load | Power factor | Efficiency (%) |
|------|--------------|----------------|
| 100% | 0.86 | 95.4 |
| 75% | 0.83 | 95.4 |
| 50% | 0.76 | 95.0 |

Notes:
Downloaded from <http://dealerselectric.com>
Generated for Model #12518XT3G444T

Performed by

Checked