



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 261033, 3" X 30" FORK STRADDLE BASE POWERED STACKER



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Battery and charger included.
- Forks lower to floor on all models.
- 5" Phenolic wheels on front, 4" swivel on rear.
- 110V AC models available. (Special order, NO cancellations or returns.)
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261033

110V AC Powered #261033AC

- Meets ANSI B56.10 specifications.
- Power Drive option available.

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#) | [Stacker Low Profile Outtrigger Option](#)

### Video



### Specifications



<b>PART NUMBER</b>	261033
<b>MODEL</b>	PESFL-76-30S
<b>TYPE</b>	Straddle Base Fork Model
<b>FRONT WHEEL</b>	(2) 5" Phenolic
<b>REAR SWIVEL CASTER</b>	(2) 4" Phenolic
<b>LIFT HEIGHT</b>	76"
<b>CAPACITY</b>	1000 lb
<b>WIDTH FORKS</b>	3"
<b>LENGTH FORKS</b>	30"
<b>BASE LEG (ID/OD)</b>	25.5"/32"
<b>OVERALL WIDTH</b>	32"
<b>OVERALL HEIGHT</b>	92"
<b>OVERALL DEPTH</b>	48"
<b>WEIGHT</b>	465 lb
<b>MADE IN THE USA</b>	

## 5th Wheel Steering Option

### 5TH WHEEL STEERING OPTION




**5th Wheel Steering Option** for easier mobility & precision steering in confined areas  
Available only on 1,500 and 2,000 lb models.  
8" locking polyurethane wheels. Spring loader handle. Can be field installed.  
Order as separate option under Part # 261099

5th wheel steering option

## Stacker Low Profile Outrigger Option

### STACKER LOW PROFILE OUTRIGGER OPTION



Stacker Low Profile Outrigger Option