



Wesco Industrial Products, Inc.

1250 Welsh Rd
North Wales, PA 19454
Phone: 800.445.5681 • Fax: 800.346.5511
Email: info@wescomfg.com

PART NO. 261037, 56" LIFT HEIGHT COUNTER-BALANCE POWERED STACKER




- Meets ANSI B56.10 specifications.
- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- 1,000 lb. maximum lift capacity.
- Remote control, floor lock, and safety screen are standard on all models.
- With a minimally charged battery, unit can be used while recharging.
- Easy to read illuminated battery status voltmeter – no extra cost!
- 12V DC battery
- Battery and charger included.
- Applications include:
 - Loading and unloading trucks.
 - Positioning dies.
 - Feeding material to presses.
- 25" long forks standard.
- 30" long fork models available, 850 lb. max. capacity.
- Order enough weight kits for your planned load.
- AC models not available.
- Power lift manual drive standard, optional power drive available.

Note: Counter-Balance Stackers require appropriate counter-weights. (see counter weight graph)

[Video](#) | [Specifications](#)

[Video](#)





Specifications

PART NUMBER	261037
MODEL	PCBFL-56-25
LIFT HEIGHT	56"
CAPACITY	1000 lb
WHEEL	(2) 5" Polyolefin
WHEEL REAR SWIVEL CASTERS	(2) 5" Polyolefin Wheel
WIDTH FORKS	3"
LENGTH FORKS	25"
LOAD CENTER	13"
OVERALL WIDTH	26.5"
OVERALL HEIGHT	72"
OVERALL DEPTH	59.5"
WEIGHT	560 lb. Without Counter Weights

Part #	261041	261042	261043
Counterweight lbs	200	400	600
Stacker Load Capacity lbs	334	668	1000

Counterweight Graph



MADE IN THE USA