




1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 261078, 30" X 32" PLATFORM 36" O.D. FIXED BASE LIFT POWERED STACK



- 1-year warranty.
- Proven quality: Wesco® manufactured Hydraulic Cylinder.
- Meets ANSI B56.10 specifications.
- Battery and charger included.
- Platform lowered height 6".
- Reinforced frame and base
- Double chain, lift support.
- Heavy-duty pump.
- Ergonomic "D" handles.
- 5th wheel and power drive options available.
- 110V AC models available (Special order no cancellations or returns).
- To order add AC to the end of the battery powered stacker part #.

Example:

Battery Powered #261078

110V AC Powered #261078AC

[Video](#) | [Specifications](#) | [5th Wheel Steering Option](#)

### Video



## Specifications

<b>PART NUMBER</b>	261078
<b>MODEL</b>	PSPL-90-3032-30S-1.5K
<b>LIFT HEIGHT</b>	90"
<b>CAPACITY</b>	1500 lb
<b>PLATFORM WIDTH</b>	30"
<b>PLATFORM LENGTH</b>	32"
<b>LOAD CENTER</b>	18"
<b>BASE LEG (ID/OD)</b>	30"/36"
<b>OVERALL HEIGHT</b>	104"
<b>WEIGHT</b>	573 lb

**MADE IN THE USA**



## 5th Wheel Steering Option

**5TH WHEEL STEERING OPTION**



**5th Wheel Steering Option** for easier mobility & precision steering in confined areas  
 Available only on 1,500 and 2,000 lb models.  
 8" locking polyurethane wheels. Spring loader handle. Can be field installed.  
 Order as separate option under Part # 261099

5th wheel steering option