



1250 Welsh Rd
 North Wales, PA 19454
Phone: 800.445.5681 • **Fax:** 800.346.5511
Email: info@wescomfg.com

PART NO. 261104, POWERED LIFT TABLE 24" X 36", 4000 LB CAPACITY, 59" LIFT HEIGHT



- **1-year warranty.**
- Standard floor lock holds table steady for loading and unloading.
- Easy to read illuminated battery status voltmeter.
- With a minimally charged battery, unit can be used while recharging.
- Push-pull, roller and ball tops available on Wesco® 24" x 36" manual and power tables.

[Video](#) | [Specifications](#)

Video



Specifications



PART NUMBER	261104
MODEL	PLT-40-2436
CAPACITY	4000 lb
CASTER	6" Phenolic Resin Wheel (2) Swivel (2) Rigid
TABLE WIDTH	24"
TABLE LENGTH	36"
RAISED HEIGHT	59"
LOWERED HEIGHT	37"
OVERALL WIDTH	24"
OVERALL HEIGHT	37"
OVERALL DEPTH	39.25"
WEIGHT	597 lb

MADE IN THE USA

