



1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: info@wescomfg.com

PART NO. 272736, STANDARD DELUXE MODEL TRUCK



- 8" raised height.
- 3" lowered height.
- 6" wide forks.

- **Deluxe Models feature 5 year pump warranty and 5,500 lb. capacity**
- Pump overload bypass.
- Rubber coated handle.
- 200° steering.
- Tapered fork tips.
- Adjustable fork tie rods.
- Exit rollers.
- 8 gauge 6" wide reinforced forks.
- 5 year pump warranty.
- 8" non-marking moldon polyurethane steering wheel.
- 3" non-marking moldon polyurethane load wheels.

Specifications

PART NUMBER	272736
FORK DIMENSION	27" x 36"
CAPACITY	5500 lb
W1	27"
L1	36"
W2	6"
L2	51"
WHL1	8"
WHL2	3"
H1	48"



H2

3"

H3

8"

WEIGHT

151 lb