




1250 Welsh Rd

North Wales, PA 19454

Phone: 800.445.5681 • Fax: 800.346.5511

Email: [info@wescomfg.com](mailto:info@wescomfg.com)

## PART NO. 273203, BATTERY OPERATED VALUE LIFT STACKER



- Adjustable 4" wide x 25.5" long forks.
- Two 5" polyurethane swivel casters with brake and two 3" polyurethane rigid wheels.
- Lift height: 47".
- Chrome plated rails and handles.
- UL approved charger.
- Sealed maintenance-free battery.
- Keyed on/off switch.
- Raise/lower control.
- **#272942 Optional Platform fits both Manual and Electric Value Lift Stackers. Optional, removable 22"**
- Adjustable fork width 8.25" to 21.5"

### Specifications

<b>PART NUMBER</b>	273203
<b>MODEL</b>	VLP-47
<b>CAPACITY</b>	880 lb
<b>BATTERY</b>	12 V 80 Ah Sealed
<b>SWIVEL CASTER</b>	(2) 5" Locking Polyurethane
<b>LOAD WHEEL</b>	(2) 3" Rigid Polyurethane
<b>LIFT HEIGHT</b>	3.5" to 47"
<b>LOWERED HEIGHT</b>	3.5"
<b>WIDTH FORKS</b>	4"
<b>LENGTH FORKS</b>	25.5"
<b>LOAD CENTER</b>	12.75"



<b>OVERALL WIDTH</b>	22.5"
----------------------	-------

<b>OVERALL HEIGHT</b>	55"
-----------------------	-----

<b>OVERALL DEPTH</b>	44"
----------------------	-----

<b>WEIGHT</b>	269 lb
---------------	--------