

2600 SERIES™ OVERFLOOR RACEWAY

Ordering Information

2600 Series Raceway Wire Fill Capacities for Communications

	CABLE/WIRE SIZE	O.D. (Approx. dia.)		40% FILL
		Inches	(mm)	
UNSHIELDED TWISTED PAIR	4-pair, 24 AWG, Cat 3	0.190	(4.8)	10
	4-pair, 24 AWG, Cat 5e	0.210	(5.3)	8
	4-pair, 24 AWG, Cat 6	0.250	(6.3)	5
	4-pair, 24 AWG, Cat 6a*	0.354	(9.0)	2
	25-pair, 24 AWG	0.410	(10.4)	2
COAXIAL	RG6/U	0.270	(6.9)	5
FIBER	ZipCord	0.118 x 0.236	(3 x 6)	10
	Round 4 Strand Fiber	0.187	(4.8)	10
	Round 6 Strand Fiber	0.256	(6.5)	5


2600 Series Raceway Wire Fill Capacities for Power

WIRE SIZE THHN/THWN	O.D. (Approx. dia.)		NO. OF CONDUCTORS 40% FILL
	Inches	(mm)	
14 AWG	0.111	(2.8)	29
12 AWG	0.130	(3.3)	21
10 AWG	0.164	(4.2)	13

NOTE: For additional information, refer to the Technical Section.


* Category 6 augmented (6a) cable for 10 gigabit ethernet - max allowed cable diameter per addenda No. 11 ANSI TIA/EIA 568-B.2.

2600-10 Raceway Base & Cover




Cover: .050" galvanized steel.
Base: .040" (1.0mm) galvanized steel. Packed five 10' (3m) lengths per carton. Base has 9/32" (7.1mm) diameter mounting holes on centers of approximately 8" (203mm).

2611 90° Flat Elbow




For right angle turns on the same surface.

656 Cover Removal Tool



For removing cover of 1500 and 2600 Series Overfloor Raceways.


2642D Junction Box



May be used with 1500 and/or 2600 Series Raceway as a cross, tee, or elbow. Cover has 1/2" trade size KO. Base has 1/2" and 3/4" concentric KO to enable connection to floor, outlet boxes or under floor duct systems (use Chase nipple - not included). Two 2600WC Wire Clips included.


NOTE: Box covers are manufactured of UL Listed Noryl plastic, gray textured finish.

2600WC Wire Clip




For holding conductors in place.

2602 Fiber Bushing



Protects wires from abrasion. Slips into open end of 2600 Series Raceway where it enters a fitting.

2686FO Transition Feed Fitting




Eliminates offsetting 2400 Series Raceway in connecting with surface panel boxes. Has 3/4" and 1" concentric trade size KOs with 1" trade size KO elongated so adjustment from surface to center of bushing is 1" (25mm) to 1 5/8" (41mm) maximum. Has twistouts for transition to 1500 and 2600 Series Raceway.

NOTE: Box covers are manufactured of UL Listed Noryl plastic, gray textured finish.

PLUGMOLD® 2400 SERIES™


Plugmold 2400 Series Ordering Information (continued)

V2427GT Duplex Receptacle




3-wire, 20A, 125V, NEMA 5-20R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors. Ivory receptacle with ivory trim plate.

IG2427GT Isolated Ground Duplex Receptacle




3-wire, 20A, 125V NEMA 5-20R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors. Orange receptacle with ivory trim plate.

V2427GA Duplex Receptacle




3-wire, 15A, 125V, NEMA 5-15R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors. Ivory receptacle with ivory trim plate.

IG2427GA Isolated Ground Duplex Receptacle




3-wire, 15A, 125V NEMA 5-15R. Provided with 10 1/2" (267mm) pigtails and inline splice connectors. Orange receptacle with ivory trim plate.

2686FO Transition Feed Fitting



Eliminates offsetting V2400 in connecting with surface panel boxes. Has 3/4" and 1" concentric trade size KOs with 1" trade size KO elongated so adjustment from surface to center of bushing is 1" (25mm) minimum to 1 5/8" (41mm) maximum. Has twistouts for transition to Pancake 1500 and 2600 Series Raceway.

V2426 Lamp Holder




Medium base lamp holder 660W, 250V. Black, general purpose phenolic.

2400 SERIES™ RACEWAY

2400 Series Raceway Fittings Ordering Information (continued)

Extra Deep Device Box



PART NUMBERS:
V2444-2 (Ivory)

2444-2FW (Fog White)

Two-gang device box with extra depth to allow installation of cabling that requires greater bend radius and storage. Cover has

twistout on all four sides for 2400 Series Raceway. Base has knockout to enable extension from existing single-gang flush wall box and 1/2" and 1" concentric trade size KOs. Accepts industry standard faceplates for electrical and communication devices.


Device Box


PART NUMBERS:
V2444-2LS (Ivory)

2444-2LSFW (Fog White)

Two-gang labor saving, over-the-raceway device box. Cover has twistout on all four side for 2400 Series Raceway. Accepts industry standard faceplates for electrical and communication devices.

Device Box



PART NUMBERS:
V2448 (Ivory)

2448-FW (Fog White)

One-gang device box. Cover has twistout for 2400 Series Raceway on each side and one twistout

for 500 and 700 Series Raceway on the top and bottom. Base has knockout to enable extension from existing single-gang, flush wall box and 1/2" trade size KOs. Accepts industry standard faceplates for electrical and communication devices.

Device Box



PART NUMBERS:
V2448-2 (Ivory)

2448-2FW (Fog White)

Two-gang device box. Cover has twistouts on all four sides for 2400 Series Raceway. Base has knockout to enable extension from existing single-gang, flush wall box and 1/2" trade size KOs. Accepts industry standard faceplates for electrical and communication devices.

Back Feed Fitting


PART NUMBERS:
V2451H (Ivory)

2451H-FW (Fog White)


Feeds 2400 Series Raceway from an existing outlet box. Includes 1/2" trade size male bushing and lock nut washer for grounding.


Bridge Fitting

PART NUMBERS:
V2475D (Ivory)

2475D-FW (Fog White)



Allows 2400 Series Raceway runs to bridge over existing installations of 2400, 500, and 700 Series Raceways.

V2489 Side Reducing Connector




Connects 2400 Series Raceway with 500 Series Raceway.

V2489TB Transition Box



Connects existing installations of 2100 Series Raceway to 2400 Series Raceway.

2686FO Transition Feed Fitting



Eliminates need to offset 2400 Series Raceway when connecting with surface panel boxes. Has 3/4" and 1" concentric trade size KOs with 1" trade size KO elongated so adjustment from surface to center of bushing is 1" (25mm) minimum to 1 5/8" (41mm) maximum. Has twistouts for transition to 1500 and 2600 Series Pancake Raceways.

NOTE: Parts identified with this symbol are Certified to Canadian Safety Standards for sale in Canada. When ordering these products, add "C" to the color prefix to denote the Canadian versions, i.e. "CV2444".

2600 SERIES™ OVERFLOOR RACEWAY

Ordering Information

2600 Series Raceway Wire Fill Capacities for Communications

	CABLE/WIRE SIZE	O.D. (Approx. dia.)		40% FILL
		Inches	(mm)	
UNSHIELDED TWISTED PAIR	4-pair, 24 AWG, Cat 3	0.190	(4.8)	10
	4-pair, 24 AWG, Cat 5e	0.210	(5.3)	8
	4-pair, 24 AWG, Cat 6	0.250	(6.3)	5
	4-pair, 24 AWG, Cat 6a*	0.354	(9.0)	2
	25-pair, 24 AWG	0.410	(10.4)	2
COAXIAL	RG6/U	0.270	(6.9)	5
FIBER	ZipCord	0.118 x 0.236	(3 x 6)	10
	Round 4 Strand Fiber	0.187	(4.8)	10
	Round 6 Strand Fiber	0.256	(6.5)	5


2600 Series Raceway Wire Fill Capacities for Power

WIRE SIZE THHN/THWN	O.D. (Approx. dia.)		NO. OF CONDUCTORS 40% FILL
	Inches	(mm)	
14 AWG	0.111	(2.8)	29
12 AWG	0.130	(3.3)	21
10 AWG	0.164	(4.2)	13

NOTE: For additional information, refer to the Technical Section.


* Category 6 augmented (6a) cable for 10 gigabit ethernet – max allowed cable diameter per addenda No. 11 ANSI TIA/EIA 568-B.2.

2600-10 Raceway Base & Cover




Cover: .050" galvanized steel.
Base: .040" (1.0mm) galvanized steel. Packed five 10' (3m) lengths per carton. Base has 9/32" (7.1mm) diameter mounting holes on centers of approximately 8" (203mm).

2611 90° Flat Elbow




For right angle turns on the same surface.

656 Cover Removal Tool



For removing cover of 1500 and 2600 Series Overfloor Raceways.


2642D Junction Box



May be used with 1500 and/or 2600 Series Raceway as a cross, tee, or elbow. Cover has 1/2" trade size KO. Base has 1/2" and 3/4" concentric KO to enable connection to floor, outlet boxes or under floor duct systems (use Chase nipple – not included). Two 2600WC Wire Clips included.


NOTE: Box covers are manufactured of UL Listed Noryl plastic, gray textured finish.

2600WC Wire Clip




For holding conductors in place.

2602 Fiber Bushing



Protects wires from abrasion. Slips into open end of 2600 Series Raceway where it enters a fitting.

2686FO Transition Feed Fitting



Eliminates offsetting 2400 Series Raceway in connecting with surface panel boxes. Has 3/4" and 1" concentric trade size KOs with 1" trade size KO elongated so adjustment from surface to center of bushing is 1" (25mm) to 1 5/8" (41mm) maximum. Has twistouts for transition to 1500 and 2600 Series Raceway.

NOTE: Box covers are manufactured of UL Listed Noryl plastic, gray textured finish.