


RC4 SERIES™ POKE-THRU DEVICES



RC4 Series™ Surface Style Poke-Thru Devices provide two (2) 20 Amp duplex power devices and four (4) ports of communication.




Download this product's PEP ecopassport, environmental product declaration at www.legrand.us/resources-and-downloads. This declaration conforms with ISO 14025 and 14040 and is in alignment with EN 15804.

CODE REFERENCE

cULus Listed Metallic Outlet Boxes:
File E2961 Guide QCIT.

cULus Listed Nonmetallic Outlet Boxes & Fittings Classified for Fire Resistance:
File R8209 Guide CEYY.

Meets Article 300.21, 300.22(C) & 314 of NEC.




RC4 Series Poke-Thru Device (RC4CTCBS).

HOLE DIAMETER

Minimum:	4" (102mm)
Maximum:	4 1/8" (105mm)

RC4 Series Poke-Thru Devices
Ordering Information


RC4STC Insert Assembly with Disposable Plate



Comes complete with four prewired 20A receptacles. Use RC4STC with RC4C Series Covers.

NOTE: If wiring for Isolated Ground, attach orange IG label (supplied).

Slide Holder



PART NUMBERS:

RC4SHTCGY (Gray)
RC4SHTCBK (Black)
RC4SHTCBS (Brass)
RC4SHTCAA (Aluminum)

Nonmetallic slide holder assembly.

NOTE: Assembled with scrub water gasket.
For use on tile or carpet floors.

COLOR OPTIONS




RC4 Series parts are available in gray "GY", black "BK", brushed aluminum "AL", brass "BS", brass-colored finish "AB" and an aluminum-colored finish "AA".

RC4 SERIES™ POKE-THRU DEVICES

RC4 Series Poke-Thru Devices Ordering Information (continued)


Poke-Thru Controlled Receptacle


PART NUMBERS:

RC4SHTCBK2CR (Black)
RC4SHTCBS2CR (Brass)
RC4SHTCGY2CR (Gray)
RC4SHTCAA2CR (Aluminum)

Nonmetallic slide holder assembly with controlled receptacle markings. Markings are located in a recess pad and are permanent, indicating the duplex receptacle below has been wired up to comply with 2014 NEC, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in Black (BK) Brass (BS), Gray (GY) and Aluminum (AA). On circuit "A" duplex receptacles are controlled. Slide holder to be used with the RC4ATC & RC4CTC units.


Poke-Thru Controlled Receptacle


PART NUMBERS:

RC4SHTCBK4CR (Black)
RC4SHTCBS4CR (Brass)
RC4SHTCGY4CR (Gray)
RC4SHTCAA4CR (Aluminum)

Nonmetallic slide holder assembly with controlled receptacle markings. Markings are located in a recess pad and are permanent, indicating both of the duplex receptacles below have been wired up to comply with 2014 NEC, CA Title 24 and ASHRAE Energy Efficiency Standard 90.1. Available in Black (BK), Brass (BS), Gray (GY) and Aluminum (AA). Both circuit duplex receptacles are controlled. Slide holder to be used with the RC4ATC and RC4CTC units.

Finish Flange & Slide Holder Assembly



PART NUMBERS:

RC4CTCAA (All Aluminum)
RC4CTCAB (All Brass)
RC4CTCGY (Gray)
RC4CTCBK (Black)
RC4CTCAL (Aluminum)
RC4CTCBS (Brass)

Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes Ortronics TracJack Mounting adapters and Ortronics Series II Communication Housing. Modular jacks sold separately.

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

Assembled Poke-Thru Device


PART NUMBERS:

RC4ATCAA (All Aluminum)
RC4ATCAB (All Brass)
RC4ATCGY (Gray)
RC4ATCBK (Black)
RC4ATCAL (Aluminum)
RC4ATCBS (Brass)


Unit includes four prewired TR 20A receptacles. Each duplex receptacle is wired as a separate circuit. The duplex can be wired as a standard receptacle or isolated ground. Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes Ortronics TracJack Mounting adapters and Ortronics Series II Communication Housing. Modular jacks sold separately.

NOTE: Assembled with scrub water gasket. For use on tile or carpet floors.

NOTE: If wiring for Isolated Ground, attach orange IG label (supplied).


NOTE: RC4 Series poke-thru devices require a 4" (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8" minimum.

Abandonment Plate


PART NUMBERS:

RC4APTCGY (Gray)
RC4APTCBK (Black)

COM75 Communication Adapter



Provides two 3/4" trade size threaded openings to accommodate conduit connections.