

DATA SHEET

Premium Efficiency Motor: **PEWWE60-9-405T**

60 Hz

WorldWide Electric Corporation

1 (800) 808-2131

Worldwideelectric.net



Document Generated: 15-Feb-2023
Document ID:

Customer:

MOTOR INFORMATION	
HP	60
RPM	900
Phase	3
Frequency	60 Hz
Voltage	230/460 V
Frame Size	405T
Enclosure	TEFC
Degree of Protection	IP55
Service Factor	1.25
Poles	8
Full Load Speed	890
Insulation Class	F
Temp Rise	80°C
NEMA Code Letter	G
Duty Cycle	S1 / Continuous
Slip	1.11%
NEMA Design	B
Moment of Inertia	35 lb.ft.²
Locked Rotor Time (Hot)	21 seconds
Sound Pressure Level	72 dB(A)
Number of Starts	2 Cold/ 1 Hot
Max Ambient Temperature	40°C
Max Elevation	1000 m.a.s.l (3300 f.a.s.l)
Mounting	F1
Rotation	Bi-Directional
Area of Classification	Class I, Division 2, Groups A, B, C, D
Inverter Rating	10:1 CT / 20:1 VT PWM Type
Standard	NEMA MG-1
Approvals	CSA-US, CE

EFFICIENCY/POWER FACTOR		
LOAD	EFF	P. F.
100%	92.4 %	0.76
75%	92.8 %	0.72
50%	92.2 %	0.61

TORQUE		
FULL LOAD	LRT	BDT
354 lb.ft.	170 %	220 %

AMPERAGE INFORMATION		
	230V	460V
Full Load Amps	160A	80A
Locked Rotor Amps	870A	435A
No Load Current	70A	35A
Usable at 208V	177A	

BEARING INFORMATION	
DE Bearing	NU316 C3
ODE Bearing	6313 C3
Grease Type	SKF LGHP 2
DE Regreasing Interval	3400 Hours
ODE Regreasing Interval	5100 Hours

ADDITIONAL DATA	
F2 Suitable	Yes
Shaft Material	1045 Carbon Steel
Connection Diagram	230 / 460 V - 12 Lead Δ
Approximate Weight	1043 lbs.


MOTOR DRAWING

Premium Efficiency Motor: **PEWWE60-9-405T**

WorldWide Electric Corporation

1 (800) 808-2131

Worldwideelectric.net



DIMENSION - INCHES

MOUNTING					A	B	C	D	G	J	P	O	T	AB
E	2F1	2F	H	BA										
8	12.25	13.75	0.81	6.62	19.136	16.535	37.815	10	1.181	3.15	21.535	21.024	2.835	18.264

SHAFT & KEY				
S	ES	R	N-W	U
0.75	5.65	2.45	7.25	2.875

TERMINAL BOX				
AA	XB	XC	XD	XF
3	4.659	11.933	9.764	13.494

PERFORMANCE CURVES

WorldWide Electric Corporation

1 (800) 808-2131

Worldwideelectric.net




Premium Efficiency Motor:

PEWWE60-9-405T

Document Generated: 15-Feb-2023
 Document ID:

Customer:

Motor Type	PEWWE				
Output Rating (HP)	60	FL Speed	890		
Full Load Torque	354 lb.ft	LRT (%FLT)	170	460 volt FLA	80 A
Rotor Wk ²	35 lb-ft ²	BDT (%FLT)	220	230 volt FLA	160 A



NAMEPLATE / WIRING

WorldWide Electric Corporation

1 (800) 808-2131

Worldwideelectric.net



Premium Efficiency Motor:

PEWWE60-9-405T

Document Generated: 15-Feb-2023
Document ID:

Customer:

SAMPLE NAMEPLATE DATA

				3-PHASE INDUCTION MOTOR		259277 	
Model		Ser No.					
HP		S.F.		IP		Encl	
Frame		P.F.		Code		Type	
Voltage	230/460	Hz		Ins Cl		Rating	°C Amb Cont
Amps		RPM		Design		Date	
Nom.Eff.	FL	% 3/4	% 230/460V	10:1 CT	20:1 VT	PWM	VFD 1.0SF
Class I DIV. 2 Groups A B C D Class I Zone 2 IIC				Amb.40°C Amb.55°C			
				DE Brng ODE Brng Grease type: LGHP 2 (compatible with polyrex)			
50Hz		HP	V	A	rpm	1.0SF	
WorldWide Electric Corporation							

Model

HP S.F. IP Encl

Frame P.F. Code Type

Voltage Hz Ins Cl Ambient

Amps <input type="text" value="160/80"/>	RPM <input type="text" value="890"/>	Design <input type="text" value="B"/>	DE Brng NУ316 C3
Nom.Eff. <input type="text" value="FL 92.4% 3/4 92.8%"/>			ODE Brng 6313 C3
			Grease type: SKF LGHP 2